

Mills Limited Unit 2, Zodiac Business Park, High Road, Cowley Uxbridge

UB8 2GU

Contact us on: Tel: 020 8833 2626 Fax: 020 8833 2600

Email: sales@millsltd.com

Company No. 00282704 VAT No. 227082574

# Seikoh Giken HandiMate Cleaner **SM-503**

**Product Code: C05-1128 Product Images** 



## **Short Description**

Extra durable, compact and highly reliable cleaner for connector end-face suitable for cleaning in the field and factory.

## **Description**

The new, enhanced HandiMate cleaner incorporates a synthetic cleaning cloth offering greater durability, usability and improved reliability.

The SHM-503 results in a handheld connector cleaner that is strong enough for aggressive cleaning of a wider range of contaminates, soils and end-face debris.

Stable, consistent, cleaning performance regardless of operator skill thanks to its patent pending Slide-Guide connector holder.

#### **Key Features**

Extra durable, compact and highly reliable cleaner for connector end-face suitable for cleaning in the field and factory.

Automatic "Clean and Advance" tape technology provides a fresh cleaning surface for each use eliminating waste and guaranteeing long tool life.

Packaged in a handy palm sized unit, the unit enables more than 500 times cleaning.

Works with both Simplex or Duplex applications.

ESD Anti-static materials.

Supports both PC and APC endface designs.

### **Applications**

Customer premises, troubleshooting / maintenance

Pedestals, COs, Head-Ends, Routine Testing

Installation / Assembly / Production environments

Ideal cleaner for use in data centers

Supports ESD environments

Cleaning work at new network construction sites

Repair, Check and Maintenance work at Central Office facilities

Maintenance work at field transmission sites

Cleaning work for patch-cords at production assembly plants

Applicable connector

Simplex SC, FC, ST, LC and MU (For PC and APC)

Duplex LC/PC (Standard Pitch 6.25 and Narrow Pitch 5.25mm)

Duplex MU/PC (Standard Pitch width 4.5mm)

Dimensions:

H110×W68×D28 mm (Cap opened)

Weight:

80g

**Usable Life**:

Over 500 times